



G3VM-101LR

Engineering Data


LED forward current vs. Ambient temperature
IF - Ta




Continuous load current vs. Ambient temperature
IO - Ta




LED forward current vs. LED forward voltage
IF - VF




Continuous load current vs. On-state voltage
IO - VON




On-state resistance vs. Ambient temperature
RON - Ta




Trigger LED forward current vs. Ambient temperature
IFT - Ta




Turn ON, Turn OFF time vs. LED forward current
tON, tOFF - IF



Turn ON, Turn OFF time vs. Ambient temperature
tON, tOFF - Ta



Current leakage vs. Load voltage
ILEAK - VOFF



Output terminal capacitance COFF/COFF(ov) vs. Load voltage
COFF - VOFF

