
G5NB-EL

PCB Power Relay

A slim compact Relay with 7 A switching capacity



- Minimum 200,000 operations durability at 5 A (250 VAC) switching.
- IEC/EN 60335-1 conformed.
- Ambient operating temperature: max. 85°C
- IEC/EN 60079-15 conformed. (Only for G5NB-1A4-EL-HA Model)

RoHS Compliant



■Model Number Legend

G5NB-1 2 3 4 5 6 7 8

1. Number of Poles

4. Classification

1 : 1-pole

EL: High capacity and electrical durability

2. Contact Form A : SPST-NO (1a) 5. Conformity standard HA: IEC/EN 60335-1 conformed

3. Enclosure rating

6. Coil Holding Voltage

4 : Fully sealed

None: Not supported

PW: Supported

7. High temperature rating

None: Not supported

A85 : High temperature rating at 85°C

8. Packing

None: Tray Packing SP: Tube Packing

■Application Examples

Home appliances

• Industrial equipment

· Building automation

■Ordering Information

Classification	Contact form	Enclosure rating	Model	Rated coil voltage	Minimum packing unit
Single stable relay	SPST-NO (1a)	Fully Sealed	G5NB-1A4-EL-HA(-SP)		100pcs./Tray 50pcs./Tube
			G5NB-1A4-EL-HA-PW(-SP)	DC5,12,24V	
		Flux protection	G5NB-1A-EL-HA-A85		100pcs./Tray

Note 1. When ordering, add the rated coil voltage to the model number.

Example: G5NB-1A4-EL-HA DC12

Rated coil voltage

However, the notation of the coil voltage on the product case as well as on the packing will be marked as $\square\square$ VDC. Note 2. When ordering tape packing, add "-SP" to the model number.

Be sure since "-SP" is not part of the relay model number, it is not marked on the relay case.

■Ratings

●Coil

Rated voltage	Rated current (mA)	Coil resistance (Ω)	Must operate voltage (V)	Must release voltage (V)	Max. voltage (V)	Power consumption (mW)
5 VDC	40	125				
12 VDC	16.7	720	75% max.	10% min. 10 to 39%*	160% (at 23°C)	Approx. 200 Approx. 50*
24 VDC	8.3	2880		10 10 00 /0		7.55.00.00

Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

Note 2. The operating characteristics are measured at a coil temperature of 23°C.

Note 3. The "Max. voltage" is the maximum voltage that can be applied to the relay coil.

* These numbers are only for -PW type. Power consumption with Holding Voltage is approx.50mW. Please confirm the detail in page 4 Coil Voltage Reduction (Holding Voltage).

●Contacts

Item Load	Resistive load	
Contact Type	Single	
Contact material	Ag-alloy (Cd free)	
Rated load	5 A at 250 VAC, 7 A at 250 VAC	
naleu loau	5 A at 30 VDC	
Rated carry current	5 A at DC, 7 A at AC	
Max. switching voltage	250 VAC, 30 VDC	
Max. switching current	5 A at DC, 7 A at AC	

■Characteristics

Contact resistance *1		100 m Ω max.		
Operate time		10 ms max.		
Release tim	е	10 ms max.		
Insulation re	esistance *2	1,000 M Ω min.		
Dielectric	Between coil and contacts	4,000 VAC, 50/60 Hz for 1 min		
strength	Between contacts of the same polarity	750 VAC, 50/60 Hz for 1 min		
Insulation distance	Between coil and contacts	Clearance: 6 mm, Creepage: 6 mm		
Impulse withstand voltage	Between coil and contacts	10 kV (1.2 x 50 μs)		
Vibration	Destruction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)		
resistance Malfunction		10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)		
Shock	Destruction	1,000 m/s ²		
resistance	Malfunction	100 m/s ²		
Mechanical		5,000,000 operations min.		
Durability Electrical (resistive load)		Standard, Coil holding voltage type 200,000 operations at 250 VAC, 5 A 50,000 operations at 250 VAC, 7 A 100,000 operations at 30 VDC, 5 A High temperature rating type (G5NB-1A-EL-HA-A85) 100,000 operations at 250 VAC, 5 A at 85°C 50,000 operations at 250 VAC, 7 A at 85°C		
Failure rate (P level) (reference value) *3		DC5V 10mA		
Ambient operating temperature		-40°C to 85°C (with no icing or condensation)		
Ambient operating humidity		5% to 85%		
Weight		Approx. 4 g		

Note. The data shown above are initial value.

*1. Measurement conditions: 5 VDC, 1 A, voltage drop method


*2. Measurement conditions: Measured at the same points as the dielectric strength using a 500 VDC ohmmeter.

*3. This value was measured at a switching frequency of 120 operations/min.


G 5 N B-E

■Engineering Data


Maximum Switching Capacity




Durability



● Ambient Temperature vs. Maximum Coil Voltage



●Shock malfunction





Note: The maximum coil voltage refers to the maximum value in a varying range of operating power voltage, not a continuous voltage.

■Dimensions (Unit: mm)

G5NB-1A4-EL-HA(-PW) G5NB-1A-EL-HA-A85







■Approved Standards

The approval rating values for overseas standards are different from the performance values determined individually. Confirm the values before use.

●UL Recognized: 💫 (File No. E41515)

CSA Certified: (File No. LR31928)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
	SPST-NO (1a)	5 to 24V DC	7A 250V AC (General Purpose) 85°C	30,000
G5NB-1A4-EL-HA(-PW) G5NB-1A-EL-HA-A85			5A 250V AC (General Purpose) 85°C	50,000
00.12 17.121 17.100			5A 30V DC (Resistive) 85°C	6,000

●EN/IEC, VDE Certified ♠ (Certificate No. 137575)

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G5NB-1A4-EL-HA(-PW)	SPST-NO	5. 12. 24V DC	7A 250V AC (Resistive) 85°C	10.000
G5NB-1A-EL-HA-A85	(1a)	3, 12, 24V DC	5A 30V DC (Resistive) 85°C	10,000


■Precautions

●Please refer to "PCB Relays Common Precautions" for correct use.

Correct Use

Coil Voltage Reduction (Holding Voltage) after Relay operation

- If the coil voltage is reduced to the holding voltage after Relay operation, first apply the rated voltage to the coil for at least 100 ms, as shown below.
- A voltage of at least 50% of the rated voltage is required for the coil holding voltage. Do not allow voltage fluctuations to cause the coil holding voltage to fall below this level.



Applied coil voltage		Coil resistance*	Power consumption
Rated voltage	100%	125Ω (5 VDC) 720Ω (12 VDC)	Approx.200 mW
Holding voltage	50%	2880Ω (24 VDC)	Approx.50 mW

^{*} The coil resistance were measured at a coil temperature of 23°C with tolerances of ±10%.

■Other data

Creepage distance	6.0 mm
Clearance distance	6.0 mm
Insulation Material Group	III a
Type of insulation coil-contact circuit	Reinforced
open contact circuit	Micro disconnection
Rated Insulation Voltage	250V
Pollution degree	3
Rated voltage system	250V
Overvoltage category	III
Category of protection according to IEC 61810-1	RT III
Glow wire according to IEC 60335-1	<ha models="" only=""> GWT 750°C min. (IEC 60695-2-11) / GWFI 850°C min. (IEC 60695-2-12)</ha>
Tracking Index of relay base	PTI 250V min. (housing Parts)
Flammability class according to UL94	V-0

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact

Americas

https://www.components.omron.com/

Asia-Pacific

https://ecb.omron.com.sg/

Korea

https://www.omron-ecb.co.kr/

Europe

http://components.omron.eu/

China

https://www.ecb.omron.com.cn/

Japan

https://www.omron.co.jp/ecb/