


OMRON Launches UVC Disinfection Robot

-A Co-creation with Techmetics Robotics for Completely Automated, Safe and 360° Pathogen Disinfection

SINGAPORE, 15 JULY 2020: [OMRON Asia Pacific](#), a global leader in industrial automation solutions across Asia Pacific, has forayed into UVC disinfection with the launch of its robot - LD UVC. The robot is a co-creation with Techmetics Robotics- the forerunners in autonomous service robots, to enable organisations fight spread of infectious diseases effectively & conveniently.

The UVC light has been proven to be effective in breaking down the pathogens' DNA and RNA beyond recovery, thus stopping them from replicating. OMRON LD-UVC navigates autonomously and disinfects premises including the high-touch areas by eliminating 99.90% of bacteria and viruses -both airborne and droplet- by delivering the precise dosage of UVC energy.



Equipped with lasers and Passive Infrared (PIR) Motion Sensors, for obstacle detection & avoidance, the LD UVC robot manoeuvres through narrow corridors, elevators, and even automatic doors seamlessly. It also shuts off its UVC light upon human detection, ensuring impeccable safety for human beings. Suitable for indoor spaces, the robot follows a mapped route, reducing the requirement of manpower resources dedicated for manual cleaning. Features like bumper, sonar and emergency stop render additional safety. The machine has an automatic charging and smooth touch interface for control. All this makes it an ideal gadget for facility management across hospitals, hotels, malls, event venues, airports, corporate office to name just a few. With a simple integration of software, the robot gets up and running in minimal installation time and needs no modifications or construction of the premises.

Main Features

- 8 UVC lamps placed in a circle provide full 360° coverage to eliminate 99.90% of bacteria and viruses
- PIR Motion Sensors on all four sides to detect human presence and trigger UVC light to turn off immediately
- Lidar Sensors for toe, high level, and overhanging obstacles detection to avoid collisions
- Stainless steel Lamp Guard to safeguard the lamp from collision against protruding objects
- Built-In Audio & Visual Buzzer, speech and display to provide warning alert before turning on UVC light
- 13 hours battery life for robot movement and 3.5 hours for UV operation

Elaborating more on the rationale of the launch, **Mr. Takehito Maeda, Managing Director of Industrial Automation Business, OMRON Asia Pacific** says, **“Given the utmost significance of sanitization and disinfection in the post COVID-19 era, we believe the robot will yield a great value to organizations who are struggling to find the right, effective, less labour-intensive and long-term solutions to ensure their premises are safe and germ-free. Driven with the mission to contribute to a better society by identifying social needs, OMRON seeks to collaborate with capable & like-minded partners to come up with innovative solutions. Our collaboration with Techmetics Robotics signifies the same.”**

“OMRON is one of our most trusted partners in the mobile robot domain. With the introduction of UVC application, we have taken a significant leap together to cater to a very important social need by empowering the organisations with an advanced and effective solution to manage the COVID-19 threat.” Said **Mr. Mathan Muthupillai, Founder and CEO of Techmetics Robotics.**

The integration of UVC technology is just another example of the flexibility and adaptability inherent in OMRON mobile robots. With the largest install base in the world, OMRON mobile robots have been deployed in thousands of applications across multiple industries such as material handling, hospitability, automotive manufacturing to name just a few.

About OMRON Corporation

As a leading company of automation centered on its propriety Sensing & Control + Thinking technologies, OMRON Corporation is engaged in a wide range of business, including control equipment, electronic components, social systems, healthcare and the environment. OMRON, founded in 1933, has approximately 30,000 employees worldwide and provides products and services in approximately 120 countries and regions.

- For more information, visit OMRON's website www.omron.asia
- For more information about the robot, visit [LD UVC microsite](#)



About Techmetics Robotics

Techmetics Robotics is the pioneer in Autonomous Mobile Robots (AMR) solutions for service industries such as Healthcare, Hospitality, Assisted living, Casino and Retail industries. The company created 10 various mobile robot solutions for service industry's needs. Techmetics Robotics is on a mission to provide end-to-end autonomous delivery of goods. The company created a safe and powerful autonomous solution that can work in both public spaces and dynamic environments. The company established its operations in 7 countries worldwide through its direct offices and strong distributors network.

- For more information, visit Techmetics Robotics website www.techmetics-group.com



Media Contacts

OMRON Corporate Communications Team:

Ankur Bhat, ankur.bhat@omron.com

Kiti Kui, kiti.kui@omron.com